


# LSR II Configuration

Hoeschst 33342 Red  
670/14


BUV 496  
Live/Dead Aqua\*



Alexa 350  
DAPI\*  
Hoeschst 33342 Blue  
Hoeschst 333258  
Live/Dead Blue

BUV395  
379/28


APC-H7  
APC-Cy7  
APC-eFluor 780



Alexa 700

BV605 610/20 575LP  
BV711 710/50 685LP


BV570



BV 510  
BD Horizon V500  
AmCyan  
CFP  
Live/Dead Aqua\*

BV570 585/42 575LP  
BV605 610/20 575LP

BV 421  
Pacific Blue  
BD Horizon V450  
Live/Dead Violet  
DAPI\*



FITC  
GFP  
Alexa 488  
YFP

7AAD  
PerCP  
PerCP-Cy5.5  
PerCP eFluor 710

PI  
PE-CF594  
PE-Alexa 610  
PE-Texas Red

PE  
Alexa 532  
PyroninY  
RFP (if not too weak)  
tdTomato (if not too weak)

SSC

\* Approximate MFI can be detected well by other PMTs